



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PVC312 SCH 40 3-1/2" 10' PVC Conduit

Heritage Plastics

| | |
|------------------|--|
| Catalog Number | PVC312 |
| Manufacturer | Heritage Plastics |
| Description | PVC Conduit, Underground or Aboveground Application, Gray Color, 3.486 In Conduit Inner Diameter, 4.000 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 630 FT/PK Package Quantity, Belled End;Corrosion Resistant;Rust Resistant;Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 40 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 3-1/2 In Trade Size, 0.226 In Wall Thickness, 1.744 LB Weight |
| Weight per unit | 1.7 (lbs/each) |
| Product Category | PVC Conduit, Fittings, & Boxes |

Descriptions

| | |
|-------------|-------------------------------|
| Description | SCH 40 3-1/2" 10' PVC CONDUIT |
|-------------|-------------------------------|

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | Conduit & Raceways - Pvc Conduit, Fittings, & Boxes |
|----------------------|---|

Availability

| | |
|-------------|----|
| minimum qty | 10 |
|-------------|----|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 630 |
| Weight Per foot | 1.744 |