


PVC Rigid Schedule 40 Conduit

- Conforms to UL 651 and NEMA TC 2
- Sunlight resistant per UL 651
- Listed for 90° C conductors or cable
- Product manufactured with one integral solvent-weld bell standard per length



Trade Size	10-foot Length		20-foot Length		Approximate Weight per 100' (lbs)
	Part Number	Crate Quantity (ft)	Part Number	Crate Quantity (ft)	
½	4005010	6,000	4005020	12,000	17
¾	4007510	4,400	4007520	8,800	22
1	4010010	3,600	4010020	7,200	33
1¼	4012510	3,300	4012520	6,600	44
1½	4015010	2,250	4015020	4,500	53
2	4020010	1,400	4020020	2,800	73
2½	4025010	930	4025020	1,860	116
3	4030010	880	4030020	1,760	161
3½	4035010	630	4035020	12,60	194
4	4040010	570	4040020	1,140	229
5	4050010	380	4050020	760	311
6	4060010	260	4060020	520	403
8*	4080010	140	4080020	280	607

Trade Size	Dimensions (in)					
	Average OD	Minimum Average ID	Minimum Wall Thickness, T	Bell Entrance A	Bell Bottom B	Bell Length C
½	0.840	0.578	0.109	0.852	0.836	1.75
¾	1.050	0.780	0.113	1.064	1.046	2.25
1	1.315	1.004	0.133	1.330	1.310	2.25
1¼	1.660	1.335	0.140	1.677	1.655	2.25
1½	1.900	1.564	0.145	1.918	1.894	2.75
2	2.375	2.021	0.154	2.393	2.369	4.00
2½	2.875	2.414	0.203	2.890	2.868	4.00
3	3.500	3.008	0.216	3.515	3.492	4.00
3½	4.000	3.486	0.226	4.015	3.992	4.00
4	4.500	3.961	0.237	4.515	4.491	5.00
5	5.563	4.975	0.258	5.593	5.553	5.75
6	6.625	5.986	0.280	6.658	6.614	6.50
8*	8.625	7.853	0.322	8.670	8.610	6.50

*UL 651 does not include 8"

