



GE
Lighting

23733 - Q500T3/CL

GE Quartzline® T2.5 - Stage & Studio



GENERAL CHARACTERISTICS

Lamp Type	Halogen - Double-Ended
Bulb	T2.5
Base	Recessed Single Contact (R7s)
Filament	C-8
Bulb Finish	Clear
Rated Life	2000.0 hrs
Primary Application	Stage & Studio

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	10550.0
Color Temperature	3000.0 K
Nominal Initial Lumens per Watt	21

ELECTRICAL CHARACTERISTICS



Wattage	500.0
Voltage	130.0
Burn Position	Horizontal

DIMENSIONS

Maximum Overall Length (MOL)	4.6880 in(119.1 mm)
Bulb Diameter (DIA)	0.312 in(7.9 mm)
Light Center Length (LCL)	2.250 in(57.2 mm)

PRODUCT INFORMATION

Product Code	23733
Description	Q500T3/CL
ANSI Code	DVS
Standard Package	Case
Standard Package GTIN	10043168237335
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168237338



CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
 - Dispose of lamp in a closed container.
 - Do not use lamp if outer glass is scratched or broken.

Warning

- Lamp emits UV radiation which may cause eye/skin injury. RG-3
 - Avoid exposure of eyes and skin to unshielded lamp.
- Risk of Electric Shock
 - Turn power off before inspection, installation or removal.
- Risk of Burn
 - Allow lamp to cool before handling.
 - Turn power off before installing lamp.
- Risk of Fire
 - Fire Hazard! Do not use in Torchieres or other indoor residential fixtures.
 - Keep combustible materials away from lamp.
 - Use in enclosed fixture rated for this product.
- Pressurized lamp--unexpected rupture may cause injury, fire, or property damage
 - Do not exceed 110% of rated voltage.
 - Do not touch glass with bare hands.
 - Do not use lamp if outer glass is scratched or broken.
 - Operate lamp only in specified position -- see instructions.
 - Use eye protection when handling lamp.
 - Use in enclosed fixture rated for this product.