
QB2W

Twin 75 watt Quartz Bullet floods come pre-assembled and pre-wired on C103 Mounting plate. Lamps supplied.

Color: White

Weight: 2.1 lbs





Created: 11/16/2013

Lamp Info		Ballast Info	
Туре:	T-4	Туре:	N/A
Watts:	75W	120V:	N/A
Shape/Size:	N/A	208V:	N/A
Base:	N/A	240V:	N/A
ANSI:	N/A	277V:	N/A
Hours:	1,500	Input Watts:	75W
Lamp Lumens:	1,500	Efficiency:	100%
Efficacy:	20 LPW		

Technical Specifications

UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

Housing:

Precision die cast aluminum, 1/2" NPS threaded arm with locking swivel and EZ Grip lock nut fits all standard mounting covers.

Lens Gasket:

High temperature silicone gasket stays in place during relamping.

Reflector:

Semi-specular anodized aluminum.

Sockets:

Porcelain bi-pin GY 8 base with gold plated contacts and 250° C socket wires.

Lens:

Thick, tempered glass.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Replacement Lamps:

Installation:

Twin 75w Flood Kit pre-assembled on C103 plate for easy installation.

Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.



LIGHTING Tech Help Line: 888 RAB-1000 Copyright ©2013 RAB Lighting, Inc. All Rights Reserved