

# Eaton QBGFEP2030

Catalog Number: QBGFEP2030

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 30A, 10 kAIC, Two-pole, 120/240V, Non-Interchangeable, QBGF

## General specifications



Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFEP2030
UPC	Product Length/Depth
786679145173	5.6 in
Product Height	Product Width
0.7 in	2.4 in
Product Weight	Certifications
0.7 lb	UL 943
Catalog Notes	
HACR rated	

## Physical Attributes

### Circuit breaker type

QBGF

### Number of poles

Two-pole

### Type

Ground fault circuit breaker

## Performance Ratings

### Amperage Rating

30 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Voltage rating

120/240 V

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

### Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QBGFEP2030](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)