

Specifications

Eaton QBGFT1020

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#14-10 Cu, #12-10 Al,QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1020
UPC	786680130960
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
PRODUCT TYPE	GFCI circuit breakers

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous

SPECIAL FEATURES	5 mA Trip Sensitivity
-------------------------	-----------------------

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT1020
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton QBGFT1020

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#14-10 Cu, #12-10 Al,QBGF

General specifications

PRODUCT NAME	Eaton QB GFCI circuit breaker
CATALOG NUMBER	QBGFT1020
UPC	786680130960
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	1 year
CERTIFICATIONS	UL 489
PRODUCT TYPE	GFCI circuit breakers

Physical Attributes

CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Single-pole
TYPE	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	10 kAIC
TRIP TYPE	Non-Interchangeable
TRIP RATING	5 mA trip sensitivity
VOLTAGE RATING	120/240 V

Miscellaneous

SPECIAL FEATURES	5 mA Trip Sensitivity
-------------------------	-----------------------

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBGFT1020
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

