



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **QBGFT1020 Type QB 5MA GF BRKR 20A /1 Pole 120/240V 10kaic** *Eaton Corp*

Catalog Number	QBGFT1020
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 20 A, Non-Interchangeable Tripping Mechanism, Bolt-On, 120/240 V Ac, 1 In Overall Height, 1 In Overall Length, 1 In Overall Width, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	On Circuit Breakers

### **Features**

amperage rating	20 A
dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
Poles	1
Trip Type	Non-Interchangeable

### **Descriptions**

Description	TYPE QB 5MA GF BRKR 20A /1 POLE 120/240V 10KAIC
extra long description	ETN QBGFT1020 QB, 5MA GF 20A /1 POL
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Special Features	5 mA Trip Sensitivity

### **Manufacturer Information**

GTIN	00786680130960
UPC	786680130960

### **Taxonomies, Classifications, and Categories**

Category Description	PANELBOARD BRANCH BREAKERS
Type	GFCI circuit breakers

### **Packaging**

Carton	1
Weight Per each	0.4

### **Uses, Certifications, and Standards**

Application	Marine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper Converged
standard	UL 489