

# Eaton QBGFT1025

Catalog Number: QBGFT1025

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 25A, 10 kAIC, Single-pole, 120/240V, Non-Interchangeable, 5 mA Trip sensitivity, QBGF

Photo is representative

## General specifications

Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFT1025
UPC	Product Length/Depth
786680130977	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.5 lb	1 year
Certifications	
UL 489	



## Physical Attributes

**Circuit breaker type**  
QBGF

**Mounting Method**  
Bolt-on

**Number of poles**  
Single-pole

**Type**  
Ground fault circuit breaker

## Performance Ratings

**Amperage Rating**  
25 A

**Interrupt rating**  
10 kAIC

**Trip Type**  
Non-Interchangeable

**Trip rating**  
5 mA trip sensitivity

**Voltage rating**  
120/240 V

## Miscellaneous

**Special features**  
5 mA Trip Sensitivity

## Resources

**Brochures**  
[Loadcenters and Circuit Breakers](#)

**Specifications and datasheets**  
[Eaton Specification Sheet - QBGFT1025](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)