

# Eaton QBGFT1040

Catalog Number: QBGFT1040

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,40A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,#8 Cu, #8–6 Al,QBGF

## General specifications



Photo is representative

Product Name

Eaton QB GFCI circuit breaker

Catalog Number

QBGFT1040

UPC

786680130991

Product Length/Depth

1 in

Product Height

1 in

Product Width

1 in

Product Weight

0.5 lb

Warranty

1 year

Certifications

UL 489

## Physical Attributes

### Circuit breaker type

QBGF

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

### Wire size

#8 Cu

#8–6 Al

## Performance Ratings

### Amperage Rating

40 A

### Interrupt rating

10 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBGFT1040](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)