Specifications



Photo is representative

Eaton QBGFT2015

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 15A, 10 kAIC, Two-pole, 120/240V, Common trip, 5 mA Trip sensitivity, #14–10 Cu, #12–10 Al, QBGF

General specifications		
PRODUCT NAME	Eaton QB GFCl circuit breaker	
CATALOG NUMBER	QBGFT2015	
UPC	786676026703	
PRODUCT LENGTH/DEPTH	4.5 in	
PRODUCT HEIGHT	2 in	
PRODUCT WIDTH	2.75 in	
PRODUCT WEIGHT	0.6 lb	
WARRANTY	1 year	
CERTIFICATIONS	UL 489	
CATALOG NOTES	HACR rated	



Physical Attributes	
CIRCUIT BREAKER TYPE	QBGF
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Two-pole
ТҮРЕ	Ground fault circuit breaker
WIRE SIZE	#14-10 AWG Cu #12-10 AWG Al

Performance Ratings		
AMPERAGE RATING	15 A	
INTERRUPT RATING	10 kAIC	
TRIP TYPE	Common trip	
TRIP RATING	5 mA trip sensitivity	
VOLTAGE RATING	120/240 V	

Miscellaneous	
SPECIAL FEATURES	5 mA Trip Sensitivity

Resources	
SPECIFICATIONS AND	Eaton Specification Sheet -
DATASHEETS	QBGFT2015

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.









