

# Eaton QBGFT2050

Catalog Number: QBGFT2050

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,50A,10 kAIC,Two-pole,120/240V,Common trip,5 mA Trip sensitivity,#8-6 Cu, #6-4 Al,QBGF

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton QB GFCI circuit breaker	QBGFT2050
UPC	Product Length/Depth
786676026697	6.5 in
Product Height	Product Width
2 in	3.5 in
Product Weight	Warranty
0.8 lb	1 year
Certifications	Catalog Notes
UL 489	HACR rated

## Physical Attributes

### Circuit breaker type

QBGF

### Mounting Method

Bolt-on

### Number of poles

Two-pole

### Type

Ground fault circuit breaker

### Wire size

#6–4 Al

#8–6 Cu

## Performance Ratings

### Amperage Rating

50 A

### Interrupt rating

10 kAIC

### Trip Type

Common trip

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBGFT2050](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)