

# Eaton QBHGFT1020

Catalog Number: QBHGFT1020

Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,22 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip Sensitivity,QBHGF

## General specifications



### Product Name

Eaton QB GFCI circuit breaker

### Catalog Number

QBHGFT1020

### UPC

786680131035

### Product Length/Depth

5 in

### Product Height

1 in

### Product Width

3 in

### Product Weight

0.4 lb

### Warranty

1 year

### Certifications

UL 489

## Physical Attributes

### Circuit breaker type

QBHGF

### Mounting Method

Bolt-on

### Number of poles

Single-pole

### Type

Ground fault circuit breaker

## Performance Ratings

### Amperage Rating

20 A

### Interrupt rating

22 kAIC

### Trip Type

Non-Interchangeable

### Trip rating

5 mA trip sensitivity

### Voltage rating

120/240 V

## Miscellaneous

### Special features

5 mA Trip Sensitivity

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - QBHGFT1020](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)