

# Specifications



## Eaton QBHW1015

Eaton QB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, 20 A, 22 kAIC, Single-pole, 120/240 V, Non-Interchangeable, Q17, QBHW

### General specifications

<b>PRODUCT NAME</b>	Eaton QB thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	QBHW1015
<b>UPC</b>	786679392003
<b>PRODUCT LENGTH/DEPTH</b>	3.9 in
<b>PRODUCT HEIGHT</b>	4.8 in
<b>PRODUCT WIDTH</b>	1.2 in
<b>PRODUCT WEIGHT</b>	0.3 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	Switching duty rated for 120V fluorescent light applications, HACR rated
<b>PRODUCT TYPE</b>	Thermal magnetic circuit breakers



Powering Business Worldwide

## Physical Attributes

<b>CIRCUIT BREAKER TYPE</b>	QBHW
<b>MOUNTING METHOD</b>	Bolt-on
<b>NUMBER OF POLES</b>	Single-pole
<b>TYPE</b>	Quicklag industrial thermal-magnetic circuit breaker

## Miscellaneous

<b>QUANTITY</b>	17
-----------------	----

## Performance Ratings

<b>AMPERAGE RATING</b>	15 A
<b>INTERRUPT RATING</b>	22 kAIC
<b>TRIP TYPE</b>	Non-Interchangeable
<b>VOLTAGE RATING</b>	120/240 V

## Resources

CATALOGS	<a href="#">Circuit Protection, Miniature Circuit Breakers and Supplementary Protectors, Volume 4, Tab 1</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHW1015</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

