



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 S 78th St.
33619-0000, FL Tampa
Phone: 813-502-0060
Fax: 000-000-0000



QBHW2045 45A 2P 22KA B BKR

Eaton Corp

Catalog Number	QBHW2045
Manufacturer	Eaton Corp
Description	Eaton QB Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 45 A, 22 Kaic, Two-Pole, 240 V, Non-Interchangeable, Q7, QBHW
Weight per unit	0.3000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	3.1000 IN X 2.0000 IN X 0.9000 IN
interrupt rating	22
Poles	Two-pole
Voltage Rating	120/240 V

Descriptions

Description	45A 2P 22KA B BKR
extra long description	ETN QBHW2045 45A 2P 22KA B BKR
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,45 A,22 kAIC,Two-pole,240 V,Non-Interchangeable,Q7,QBHW
Product Type	45A 2P 22KA B BKR

Manufacturer Information

Brand	Eaton
GTIN	00786679152478
Manufacturers Part Number	QBHW2045
UPC	786679152478

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	12
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

201 S 78th St.
33619-0000, FL Tampa
Phone: 813-502-0060
Fax: 000-000-0000

Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional
EnergyOtherGeneration - Renewable Energy - Alternative
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment - Other

standard

CSA Certified,UL Listed