



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBHW3045H QBHW3045H BKR A

Eaton Corp

Catalog Number	QBHW3045H
Manufacturer	Eaton Corp
Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-Pole, 45 A, 22 Kaic, 240 V, Bolt-On
Weight per unit	1.2 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

dimensions	3.8000 IN X 3.3000 IN X 4.4000 IN
interrupt rating	22
Poles	3
Voltage Rating	240 V - 240 V

Descriptions

Description	QBHW3045H BKR A
extra long description	ETN QBHW3045H Quicklag Thermal-Magn
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 45 A, 22 kAIC, 240 V, Bolt-on
Product Type	Quicklag Thermal-Magnetic CKT Breaker

Manufacturer Information

Brand	Eaton
GTIN	00786679393420
Manufacturers Part Number	QBHW3045H
UPC	786679393420

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	1.15



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Generation - Conventional Energy - Conventional
EnergyOtherGeneration - Renewable Energy - Alternative
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment - Other

standard

CSA Certified,UL Listed