

Eaton QC1020

Catalog Number: QC1020

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 20 A, 10 kAIC, Single-pole, 120/240 V, Thermal-magnetic, QC, Non-interchangeable

General specifications



Product Name

Eaton QC thermal magnetic circuit breaker

Catalog Number

QC1020

UPC

786679308882

Product Length/Depth

3.9 in

Product Height

4.8 in

Product Width

1.2 in

Product Weight

0.35 lb

Certifications

UL Listed
CSA Certified

Catalog Notes

Switching duty rated for 120V fluorescent light applications



Powering Business Worldwide

Physical Attributes

Circuit breaker type

QC

Number of poles

Single-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

120/240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QC1020](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)