



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## QC15ESCB BK 1PH 0.15KVA 240-32 Cu Buck Booster XFMR

*Hammond Power Solutions*

Catalog Number	QC15ESCB
Manufacturer	Hammond Power Solutions
Description	Buck-Boost Transformer, 120X240 PV, 16X32 SV
Weight per unit	8.0 (lbs/each)
Product Category	20170503150557

### Dimensions and Weight

Height	7.19
Length	5.06
Width	3.69

### Descriptions

Description	BK 1PH 0.15KVA 240-32 CU BUCK BOOSTER XFMR
extra long description	HMND QC15ESCB BK 1PH 0.15KVA 240-32
Long Description	Buck-Boost Transformer, 120x240 PV, 16x32 SV
Product Type	BK 1PH 0.15KVA 240-32 Cu
Special Features	Encapsulated transformers can be used to buck and boost voltage in single and three phase applications where supply voltages are frequently above or below nominal. These transformers can also be used in low voltage transformer application.

### Manufacturer Information

Brand	HPS Universal™
GTIN	00803423042356
Manufacturers Part Number	QC15ESCB
UPC	803423042356

### Taxonomies, Classifications, and Categories

Category Description	BUCK & BOOST TRANSFORMERS
Type	Transformer > Dry Type > Buck-Boost

### Packaging

Carton	1
Weight Per each	8



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	General purpose for raising supply voltage caused by line drop or equipment demand on the distribution system, or lower voltage caused by increased system voltages due to supply line adjustments
Enclosure	NQ0-N3R - Indoor or Outdoor
Frequency Rating	50/60
Mounting	WALL MOUNT
standard	CSA, UL, Class 1 Div II
Temperature Rating	Typical 30 Average/ 40 Maximum