



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10131 E 21st St.
74129-0000, OK Tulsa
Phone: 918-948-7825
Fax: 918-835-8085



QC3010H QC3010H BKR A *Eaton Corp*

Catalog Number	QC3010H
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 10 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.9 In Overall Height, 3.9 In Overall Length
Weight per unit	1.1 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

Features

connection	Cable-in/Cable-out
dimensions	3.9000 IN X 3.2000 IN X 4.9000 IN
Poles	Three-pole

Descriptions

Description	QC3010H BKR A
extra long description	ETN QC3010H QC3010H BKR A
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.

Manufacturer Information

GTIN	00786679240021
UPC	786679240021

Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1.05

Uses, Certifications, and Standards

Application	OtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedGeneration - Conventional Energy - Conventional EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL Listed,CSA Certified