

Eaton QC3020H

Catalog Number: QC3020H

Eaton Quicklag Type QC Industrial Thermal-Magnetic Circuit Breaker,Industrial circuit breaker,20 A,10 kAIC,Three-pole,240 V,Thermal-magnetic,QC,Non-interchangeable

General specifications



Product Name

Eaton QC thermal magnetic circuit breaker

Catalog Number

QC3020H

UPC

786679240069

Product Length/Depth

3.8 in

Product Height

4.8 in

Product Width

2.9 in

Product Weight

1 lb

Warranty

1 year

Certifications

UL Listed

CSA Certified

Physical Attributes

Circuit breaker type

QC

Number of poles

Three-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

20 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

240 V - 240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

[Eaton Specification Sheet - QC3020H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia