



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

608 Industrial Blvd
78654-0000, TX Marble Falls
Phone: 830-693-9910
Fax: 830-693-0544



QC3030H Type QC BRKR 3P 30A 240VAC Max 10kaic *Eaton Corp*

Catalog Number	QC3030H
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 30 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.9 In Overall Height, 3.8 In Overall Length
Weight per unit	1.1 (lbs/each)
Product Category	3 Pole Din Rail Mount Circuit

Features

dimensions	3.8000 IN X 3.2000 IN X 4.9000 IN
Poles	Three-pole

Descriptions

Description	TYPE QC BRKR 3P 30A 240VAC MAX 10KAIC
extra long description	ETN QC3030H TYPE QC BREAKER 3P 30A
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.

Manufacturer Information

GTIN	00786679240106
UPC	786679240106

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1.1

Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper ConvergedOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative Energy
standard	UL Listed,CSA Certified