

Eaton QCD2060

Catalog Number: QCD2060

Eaton Quicklag Type QCD Industrial Thermal-Magnetic Circuit Breaker,Industrial circuit breaker,60 A,10 kAIC,Two-pole,120/240 V,Thermal-magnetic,Cable-in/cable-out,QCD,Non-interchangeable

General specifications

Product Name	Catalog Number
Eaton QC thermal magnetic circuit breaker	QCD2060
	UPC
	786679135969
Product Length/Depth	Product Height
4 in	3 in
Product Width	Product Weight
2 in	0.905 lb
Warranty	Certifications
1 year	UL Listed
	CSA Certified



Physical Attributes

Circuit breaker type

QCD

Connection

Cable-in/cable-out

Number of poles

Two-pole

Type

Industrial circuit breaker

Performance Ratings

Amperage Rating

60 A

Interrupt rating

10 kAIC

Trip Type

Thermal-magnetic

Voltage rating

120/240 V

Miscellaneous

Options

Non-interchangeable

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - QCD2060](#)

[Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia