



# Vinyl Female Quick Disconnect For 22 - 18 AWG (.25 x .03)

By Burndy  
Catalog # [QP18F25X03D](#)

Brass Female Quick Disconnect, 18-22 AWG, Vinyl Insulated, Tin Plated.



## Application

For quickly connecting or disconnecting a terminal

## General

Connector Type	Female Quick Disconnect
EU RoHS Indicator	Yes
Insulation	Y
Insulation Type	Vinyl
Material	Brass
Plated	Y
Plating Type	Tin
Sub Brand	FINGRIP
Trade Name	FINGRIP™
Type	Disconnect Connectors
UPC	781810293195
UPC 12 Digit	7818102931955

## Dimensions

Dimension - Length Overall inch	0.87 in
Dimension - Strip Length inch	3/8 in
Dimension - Width inch	0.25 in
Dimension - Width mm	6 mm

## Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

## Conductor Related

Conductor Range	#16 AWG to #22 AWG
Conductor Size	22 - 18 AWG
Conductor Type	CU C Str-Size

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	99999

## Product Assets

[3D Models - QP18F25X03D\\_MODEL-PDF](#)  
[3D Models - QP18F25X03D\\_MODEL-IGES](#)  
[3D Models - QP18F25X03D\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50094207](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-QP18F25X03D-SPEC-EN | REV 8/2023