



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

106 Industrial Drive
71292-0000, LA West Monroe
Phone: 318-398-9757
Fax: 318-398-9704



QTP2X32T8UNVISNS *Delisted* 32WT8 Uni Volt Electronic Ballast 2lamp *Sylvania-Ledvance*

Catalog Number	QTP2X32T8UNVISNS
Manufacturer	Sylvania-Ledvance
Description	OBS49943 QTP2X32T8UNVISNSC 2 Lamp 32WT8 Instant Start Electronic Ballast, Universal Voltage, Normal Ballast Factor, 10 PK
Weight per unit	0.8300 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	0.27
Ballast Factor	88
dimnable	False
Lamp Type	FO32/XP
Minimum Starting Temperature	-20.000000000000000
Number of Lamps	2
Power Factor	>0.97
start type	Instant Start
total harmonic distortion	<10
Voltage Rating	120
Wattage	32

Dimensions and Weight

Height	1.1810000000000000
Length	9.4690000000000000
Width	1.6930000000000000

Descriptions

Description	*DELISTED* 32WT8 UNI VOLT ELECTRONIC BALLAST 2LAMP
extra long description	SYL QTP-2X32T8/UNV-ISN-SC/49943 QTP
Long Description	OBS49943 QTP2x32T8UNVISNSC 2 lamp 32wT8 Instant Start electronic ballast, universal voltage, normal ballast factor, 10 pk
Product Type	QTP2X32T8UNVISNSC 10/CS 1/Sku
Special Features	NO

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135499432
Manufacturers Part Number	QTP-2X32T8/UNV-ISN-SC/49943
UPC	046135499432

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts And Lighting Controls



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

106 Industrial Drive
71292-0000, LA West Monroe
Phone: 318-398-9757
Fax: 318-398-9704

Packaging

Carton	1
Package	10
Weight Per each	0.83

Uses, Certifications, and Standards

Application	lighting
Mounting	Tabbed
standard	FCC 47 CFR Part 18, Non-Consumer