



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2214 South 8th Street
72758-6430, AR Rogers
Phone: 479-636-4190
Fax: 479-636-5604



QTP3X32T8UNVISNS *Delisted* 32WT8 Uni Volt Electronic Ballast 3lamp *Sylvania-Ledvance*

Catalog Number	QTP3X32T8UNVISNS
Manufacturer	Sylvania-Ledvance
Description	OBS49945 QTP3X32T8UNVISNSC 3 Lamp 32WT8 Instant Start Electronic Ballast, Universal Voltage, Normal Ballast Factor, 10 PK
Weight per unit	0.9300 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	120
Ballast Factor	0.88
Minimum Starting Temperature	-20.000000000000000
Number of Lamps	3
Power Factor	>0.97
start type	Instant Start
total harmonic distortion	<10

Dimensions and Weight

Height	1.1810000000000000
Length	9.4690000000000000
Width	1.6810000000000000

Descriptions

Description	*DELISTED* 32WT8 UNI VOLT ELECTRONIC BALLAST 3LAMP
extra long description	SYL QTP-3X32T8/UNV-ISN-SC/49945 QTP
Long Description	OBS49945 QTP3x32T8UNVISNSC 3 lamp 32wt8 Instant Start electronic ballast, universal voltage, normal ballast factor, 10 pk
Product Type	QTP3X32T8UNVISNSC 10/CS 1/Sku
Special Features	NO

Manufacturer Information

Brand	Ledvance LLC
GTIN	00046135499456
Manufacturers Part Number	QTP-3X32T8/UNV-ISN-SC/49945
UPC	046135499456

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts And Lighting Controls

Packaging

Carton	1
Package	10
Weight Per each	0.93