

# ELECTRONIC CABLE RISER RATED



RISER RATED - MULTI-CONDUCTOR OVERALL SHIELDED										
TWC PART NUMBER	SW PART NUMBER	DESCRIPTION	AWG	# COND	NOM. DIAM. (inch)	PACKAGING			JACKET COLOR	UL/NEC®
						TYPE	LENGTH	lbs/1000 ft		
Burglar alarm, public address systems, intercoms, telephone stations, speakers, instrumentation & control, sunlight resistant. For power-limited circuits use except those in plenums.										
R20007.1A	57572102	22/2C STR BC OAS GRY	22	2	0.130	REELS	1000'	12	GRAY	CMR/CL3R
R20007.1B	57572101	22/2C STR BC OAS GRY	22	2	0.130	REELEX	1000'	12	GRAY	CMR/CL3R
R20007.1D	57572104	22/2C STR BC OAS GRY	22	2	0.130	REELEX	500'	12	GRAY	CMR/CL3R
R20008.1A	57786901	22/4C STR BC 2C-OAS 2C N/S GRY	22	4	0.149	REELS	1000'	9	GRAY	CMR/CL3R
R20016.1A	57572202	22/3C STR BC OAS GRY	22	3	0.138	REELS	1000'	15	GRAY	CMR/CL3R
R20030.1A	57572402	22/4C STR BC OAS GRY	22	4	0.149	REELS	1000'	18	GRAY	CMR/CL3R
R20030.1B	57572401	22/4C STR BC OAS GRY	22	4	0.149	REELEX	1000'	18	GRAY	CMR/CL3R
R20076.1A	57572502	22/6C STR BC OAS GRY	22	6	0.167	REELS	1000'	24	GRAY	CMR/CL3R
R20076.1B	57572501	22/6C STR BC OAS GRY	22	6	0.167	REELEX	1000'	24	GRAY	CMR/CL3R
R20076.1D	57572504	22/6C STR BC OAS GRY	22	6	0.167	REELEX	500'	24	GRAY	CMR/CL3R
R20024.1A	57572302	22/8C STR BC OAS GRY	22	8	0.191	REELS	1000'	30	GRAY	CMR/CL3R
R20024.1B	57572301	22/8C STR BC OAS GRY	22	8	0.191	REELEX	1000'	30	GRAY	CMR/CL3R
R20024.1D	57572304	22/8C STR BC OAS GRY	22	8	0.191	REELEX	500'	30	GRAY	CMR/CL3R
R20081.1D	57572604	22/12C STR BC OAS GRY	22	12	0.235	REELEX	500'	43	GRAY	CMR/CL3R
R30024.1A	57572702	20/2C STR BC OAS GRY	20	2	0.142	REELS	1000'	15	GRAY	CMR/CL3R
R30024.1B	57572701	20/2C STR BC OAS GRY	20	2	0.142	REELEX	1000'	15	GRAY	CMR/CL3R
R30041.1A	57572802	20/3C STR BC OAS GRY	20	3	0.151	REELS	1000'	19	GRAY	CMR/CL3R
R40013.1A	57573102	18/2C STR BC OAS GRY	18	2	0.166	REELS	1000'	20	GRAY	CMR/CL3R
R40013.1B	57573101	18/2C STR BC OAS GRY	18	2	0.166	REELEX	1000'	20	GRAY	CMR/CL3R
R40013.1C	57573104	18/2C STR BC OAS GRY	18	2	0.166	REELS	500'	20	GRAY	CMR/CL3R
R40003.1A	57572902	18/3C STR BC OAS GRY	18	3	0.177	REELS	1000'	27	GRAY	CMR/CL3R
R40003.1B	57572901	18/3C STR BC OAS GRY	18	3	0.177	REELEX	1000'	27	GRAY	CMR/CL3R
R40003.1C	57572904	18/3C STR BC OAS GRY	18	3	0.177	REELS	500'	27	GRAY	CMR/CL3R
R40005.1A	57573002	18/4C STR BC OAS GRY	18	4	0.192	REELS	1000'	33	GRAY	CMR/CL3R
R40005.1B	57573001	18/4C STR BC OAS GRY	18	4	0.192	REELEX	1000'	33	GRAY	CMR/CL3R
R40005.1C	57573004	18/4C STR BC OAS GRY	18	4	0.192	REELS	500'	33	GRAY	CMR/CL3R
R40611.1A	57573402	18/6C STR BC OAS GRY	18	6	0.240	REELS	1000'	48	GRAY	CMR/CL3R
R40611.1C	57573404	18/6C STR BC OAS GRY	18	6	0.240	REELS	500'	48	GRAY	CMR/CL3R
R40014.1A	57573202	18/8C STR BC OAS GRY	18	8	0.251	REELS	1000'	60	GRAY	CMR/CL3R
R40014.1C	57573204	18/8C STR BC OAS GRY	18	8	0.251	REELS	500'	60	GRAY	CMR/CL3R
R40075.1C	57573304	18/12C STR BC OAS GRY	18	12	0.291	REELS	500'	86	GRAY	CMR/CL3R
A50039.1A	57570502	16/2C STR BC OAS GRY	16	2	0.190	REELS	1000'	28	GRAY	CMR/CL3R
A50039.1B	57570506	16/2C STR BC OAS GRY	16	2	0.190	REELEX	1000'	28	GRAY	CMR/CL3R
A50039.1C	57570504	16/2C STR BC OAS GRY	16	2	0.190	REELS	500'	28	GRAY	CMR/CL3R
R50044.1A	57573602	16/3C STR BC OAS GRY	16	3	0.203	REELS	1000'	38	GRAY	CMR/CL3R
R50031.1A	57573502	16/4C STR BC OAS GRY	16	4	0.222	REELS	1000'	49	GRAY	CMR/CL3R
R60052.1A	57573702	14/2C STR BC OAS GRY	14	2	0.228	REELS	1000'	41	GRAY	CL3R/FPLR
R70010.1A	57644202	12/2C STR BC OAS GRY	12	2	0.276	REELS	1000'	60	GRAY	CL3R/FPLR