



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RA114 1-1/4" RT Ang CLMP

*Robroy/Ecn Korns*

Catalog Number	RA114
Manufacturer	Robroy/Ecn Korns
Description	Clamp, 1-1/4 In Trade Size, Knra Model, Angle Shape, Hot Dip Galvanized, Right Angle Connection Orientation, 53 LB/100
Weight per unit	0.5300 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

Material	MALLEABLE IRON
similar brands	Korns Clamp

### Material, Color, and Finish

Finish	HOT DIP GALVANIZED
--------	--------------------

### Descriptions

Additional Information	Applicable standard ANSI C80.1
Also Known As...	RC Clamp Parrot Beak Corn Clamp Right Angle Clamp (RC)
Commodity Description	Rigid Conduit Fittings - Steel
Description	1-1/4" RIGHT ANGLE CLAMP

### Manufacturer Information

Brand	EC-KORNS
GTIN	00784011155095
UPC	784011155095

### Taxonomies, Classifications, and Categories

Category Description	BEAM, RA, EDGE, & PARALLEL CLAMPS
Type	RIGHT ANGLE

### Packaging

Carton	1
Package	50
Standard Package	50 PER CARTON
Weight Per each	0.53

### Uses, Certifications, and Standards

Approval	UL 6, CSA C22.2
----------	-----------------

## HOT DIP GALVANIZED CLAMPS AND CONDUIT SUPPORT

### THE ORIGINAL KORNS CLAMP

Malleable iron—

Hot dip galvanized—standard. Also available with various grades of stainless steel hardware. Contact Korn's representative or factory for pricing.



### RIGHT ANGLE CONDUIT SUPPORTS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON
KNRA-3/8	3/8 RIGHT ANGLE CLAMP	25	50
KNRA-1/2	1/2 RIGHT ANGLE CLAMP	40	50
KNRA-3/4	3/4 RIGHT ANGLE CLAMP	43	50
KNRA-1	1 RIGHT ANGLE CLAMP	48	25
KNRA-1-1/4	1 1/4 RIGHT ANGLE CLAMP	53	25
KNRA-1-1/2	1 1/2 RIGHT ANGLE CLAMP	58	25
KNRA-2	2 RIGHT ANGLE CLAMP	85	25
KNRA-2-1/2	2 1/2 RIGHT ANGLE CLAMP	106	20
KNRA-3	3 RIGHT ANGLE CLAMP	110	15
KNRA-3-1/2	3 1/2 RIGHT ANGLE CLAMP	128	15
KNRA-4	4 RIGHT ANGLE CLAMP	140	10
KNRA-5	5 RIGHT ANGLE CLAMP	330	5
KNRA-6	6 RIGHT ANGLE CLAMP	375	5



### PARALLEL CONDUIT SUPPORTS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON
KNPAR-3/8	3/8 PARALLEL CLAMP	32	50
KNPAR-1/2	1/2 PARALLEL CLAMP	58	40
KNPAR-3/4	3/4 PARALLEL CLAMP	64	30
KNPAR-1	1 PARALLEL CLAMP	70	30
KNPAR-1-1/4	1 1/4 PARALLEL CLAMP	72	25
KNPAR-1-1/2	1 1/2 PARALLEL CLAMP	93	20
KNPAR-2	2 PARALLEL CLAMP	100	20
KNPAR-2-1/2	2 1/2 PARALLEL CLAMP	135	15
KNPAR-3	3 PARALLEL CLAMP	155	10
KNPAR-3-1/2	3 1/2 PARALLEL CLAMP	190	10
KNPAR-4	4 PARALLEL CLAMP	205	10



### EDGE TYPE CONDUIT SUPPORTS

CATALOG NUMBER	DESCRIPTION	WEIGHT PER 100 PIECES (lbs)	STANDARD CARTON
KNET-1/2	1/2 EDGE CLAMP	67	30
KNET-3/4	3/4 EDGE CLAMP	71	30
KNET-1	1 EDGE CLAMP	85	20
KNET-1-1/4	1 1/4 EDGE CLAMP	91	20
KNET-1-1/2	1 1/2 EDGE CLAMP	115	20
KNET-2	2 EDGE CLAMP	135	15
KNET-2-1/2	2 1/2 EDGE CLAMP	183	10
KNET-3	3 EDGE CLAMP	230	5