



RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: White

Weight: 19.9 lbs

Project:

Type:

Prepared By:

Date:

#### Lamp Info

Type: T5HO  
Watts: 324W  
Shape/Size: N/A  
Base: N/A  
ANSI: N/A  
Hours: 20,000  
Lamp Lumens: 24,008  
Efficacy: 66 LPW

#### Ballast Info

Type: Prog. Start  
120V: 3.00A  
208V: 1.77A  
240V: 1.54A  
277V: 1.33A  
Input Watts: 362W  
Efficiency: 90%

## Technical Specifications

### Listings

#### UL Listing:

Dry Locations Only. Ceiling Mount Only.

### Construction

#### Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

#### Reflector:

Aluminum High Performance brilliant bevel segmented reflectors

#### Base:

Medium Bi Pin

### Mounts:

Surface or Chain (Y Hooks included)

### Optical

#### Lamp:

T5HO (not supplied)

#### Other

#### CRI:

85

### Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

### Electrical

#### Total Watts:

6x54W

#### Input Volts:

120-277V

#### Input Amps:

3.0/1.28.

#### Ballast Factor:

1.00.

### Dimensions



### Features

Qualifies for EPA Act 2005 incentives

Post-painted, high reflective gloss white powder coat finish

High Performance, brilliant bevel segmented reflectors

Easy wiring and maintenance access panel

Rotary locking lamp holders for vibration security and easy relamping

Heavy duty 22 gauge steel Rigid strong housing with no sharp edges



RAB offers energy efficient fluorescent fixtures for large space lighting including warehouses, factories, and distribution centers. The RBAY delivers the high quality needed for these applications with strong, heavy duty 22 gauge rigid housing with no sharp edges. The superior strong-box protective foam case packaging protects the RBAY so it arrives in perfect shape and ready to install.

Color: White

Weight: 19.9 lbs

Project:

Type:

Prepared By:

Date:

#### Lamp Info

Type: T5HO  
Watts: 324W  
Shape/Size: N/A  
Base: N/A  
ANSI: N/A  
Hours: 20,000  
Lamp Lumens: 24,008  
Efficacy: 66 LPW

#### Ballast Info

Type: Prog. Start  
120V: 3.00A  
208V: 1.77A  
240V: 1.54A  
277V: 1.33A  
Input Watts: 362W  
Efficiency: 90%

## Technical Specifications

### Listings

#### UL Listing:

Dry Locations Only. Ceiling Mount Only.

### Construction

#### Housing:

Heavy duty 22 gauge steel housing and wiring box with 1/2" NPS knockouts. Painted white. Easy wiring and maintenance access panel. Includes "Y" hooks.

#### Reflector:

Aluminum High Performance brilliant bevel segmented reflectors

#### Base:

Medium Bi Pin

### Mounts:

Surface or Chain (Y Hooks included)

### Optical

#### Lamp:

T5HO (not supplied)

#### Other

#### CRI:

85

### Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

### Electrical

#### Total Watts:

6x54W

#### Input Volts:

120-277V

#### Input Amps:

3.0/1.28.

#### Ballast Factor:

1.00.

### Dimensions



### Features

- Qualifies for EPA Act 2005 incentives
- Post-painted, high reflective gloss white powder coat finish
- High Performance, brilliant bevel segmented reflectors
- Easy wiring and maintenance access panel
- Rotary locking lamp holders for vibration security and easy relamping
- Heavy duty 22 gauge steel Rigid strong housing with no sharp edges