



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RC1010F 12-10AWG #10 BLT Nyl Insld Fork TRML

Abb Installation Products, Inc

Catalog Number	RC1010F
Manufacturer	Abb Installation Products, Inc
Description	Nylon Insulated Fork Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 Awg, Color Yellow, Copper, Tin Plated
Weight per unit	0.0060 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Material	Copper
Voltage Rating	600 V
Wire Size	12-10 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Descriptions

Description	12-10AWG #10 BLT NYL INSLTD FORK TRML
extra long description	ABB RC10-10F INS NYL FORK TERM 12-1
Long Description	Nylon Insulated Fork Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated
Product Type	Ins Nyl Fork Term 12-10 NO10 Yell
Special Features	Inner bronze insulation grip sleeve lengthens flex radius of conductor and eliminates conductor creep. Nylon jacket is color-coded

Manufacturer Information

Brand	Sta-Kon
GTIN	00786210804392
Manufacturers Part Number	RC10-10F
UPC	786210804392

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Nylon Insulated Fork Terminal

Packaging

Carton	50
Weight Per each	0.006

Uses, Certifications, and Standards

standard	UL E9809 / UL E9809
----------	---------------------