



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RCD113W Radiant 3 Switch, SP/3-Way + SP + SP W

Pass & Seymour/Legrand

Catalog Number	RCD113W
Manufacturer	Pass & Seymour/Legrand
Description	Two Single Pole Switch, 3 Poles, 3 Ways, 15 A, 120/125 V Ac, Stainless Steel, White, Rocker Actuator, Box Mount, 1.29 (L) X 1.59 (W) X 3.81 (H) In, -40 °C Operating Temperature, +115 °C Operating Temperature, 0.21 LB
Weight per unit	0.2083 (lbs/each)
Product Category	Gen Purpose Switches

Features

actuator	Rocker switch
amperage rating	15
Contact Configuration	15A
Contact Rating	120
media	Yes
operating cycles	50,000 cycles minimum, resistive, inductive, tungstun filament lamp load
Poles	3

Dimensions and Weight

Size	Depth 1.43" x Width 1.29" x Height 3.81"
------	--

Descriptions

Description	RADIANT 3 SWITCH, SP/3-WAY + SP + SP W
extra long description	P&S RCD113W RADIANT 3 SWITCH, SP/3-

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007054774
UPC	785007054774

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Two Single Pole Switches & Single Pole/3-Way

Packaging

Carton	1
Package	12
Weight Per each	0.2083



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

environmental conditions	UL94 V2
Mounting	BOX
Operating Temperature	Maximum continuous +115°C, minimum -40°C
standard	cULus, UL Listed