


RDL



TECHNICAL SPECIFICATIONS:

- :: Construction: Spun aluminum with white powder coat finish
- :: Optics: White translucent acrylic lens
- :: Isolated driver for improved thermal management
- :: Output Voltage: 36VDC
- :: Input Voltage: 120V AC
- :: Dimmable down to 10% using an approved dimmer (refer to website for more information)
- :: LED: Epistar chip (COB) and driver—35,000-hour design life
- :: CRI: 90+
- :: Power Factor: 90%
- :: Suitable for damp locations
- :: Maximum ambient 104°F
- :: Total Harmonic Distortion: ≤15 %
- :: Operating temperature: 68°F~113°F
- :: UL-listed
- :: Energy Star-rated



ACCESSORIES INCLUDED



LED DOWNLIGHTS (SMOOTH TRIM)—4" & 5"/6" ROUND

CATALOG NO.		WATTS	COLOR TEMP	LUMENS	DIAMETER
RDL4-27K-WP		12W	2700K	650LM	4"
RDL4-30K-WP		12W	3000K	700LM	
RDL4-35K-WP		12W	3500K	725LM	
RDL4-41K-WP		12W	4100K	750LM	
RDL4-50K-WP		12W	5000K	800LM	
RDL4-65K-WP		12W	6500K	850LM	
RDL6-27K-WP		19W	2700K	1200LM	5"/6"
RDL6-30K-WP		19W	3000K	1250LM	
RDL6-35K-WP		19W	3500K	1275LM	
RDL6-41K-WP		19W	4100K	1300LM	
RDL6-50K-WP		19W	5000K	1350LM	
RDL6-65K-WP		19W	6500K	1400LM	



RDL



TECHNICAL SPECIFICATIONS:

- :: Construction: Spun aluminum with white powder coat finish
- :: Optics: White translucent acrylic lens
- :: Isolated driver for improved thermal management
- :: Output Voltage: 36VDC
- :: Input Voltage: 120V AC
- :: Dimmable down to 10% using an approved dimmer (refer to website for more information)
- :: LED: Epistar chip (COB) and driver—35,000-hour design life
- :: CRI: 90+
- :: Power Factor: 90%
- :: Suitable for damp locations
- :: Maximum ambient 104°F
- :: Total Harmonic Distortion: ≤15 %
- :: Operating temperature: 68°F~113°F
- :: UL-listed
- :: Energy Star-rated



ACCESSORIES INCLUDED



LED DOWNLIGHTS (SMOOTH TRIM)—4" & 5"/6" ROUND

CATALOG NO.		WATTS	COLOR TEMP	LUMENS	DIAMETER
RDL4-27K-WP		12W	2700K	650LM	4"
RDL4-30K-WP		12W	3000K	700LM	
RDL4-35K-WP		12W	3500K	725LM	
RDL4-41K-WP		12W	4100K	750LM	
RDL4-50K-WP		12W	5000K	800LM	
RDL4-65K-WP		12W	6500K	850LM	
RDL6-27K-WP		19W	2700K	1200LM	5"/6"
RDL6-30K-WP		19W	3000K	1250LM	
RDL6-35K-WP		19W	3500K	1275LM	
RDL6-41K-WP		19W	4100K	1300LM	
RDL6-50K-WP		19W	5000K	1350LM	
RDL6-65K-WP		19W	6500K	1400LM	

