

RDL-ADJ



TECHNICAL SPECIFICATIONS:

- :: Die-cast aluminum with white powder coat finish
- :: Trim ring: Integrated spun aluminum white powder coat finish
- :: Gasket: close cell Neoprene foam gasket
- :: Lens: 0.125" white translucent acrylic
- :: Isolated driver for improved thermal management
- :: CRI: 90
- :: Working Voltage: 120V AC
- :: Dimmable
- :: Tilts to 45°
- :: Can rotate after installation to align
- :: LED: EPISTAR chip (COB) and driver—35,000-hour design life
- :: Power factor: 90% +
- :: Suitable for damp locations
- :: Maximum Ambient Temperature: 104°F
- :: UL-listed
- :: Energy Star-rated



ACCESSORIES INCLUDED







Includes medium base
E-26 screw-in adaptor
that fits any standard
incandescent downlight



GU24 Adaptor that
fits any GU24 socket

LED DOWNLIGHTS (ADJUSTABLE)—4" & 5"/6" ROUND

CATALOG NO.		WATTS	COLOR TEMP	LUMENS	DIAMETER
RDL4-ADJ-27K		10W	2700K	650LM	4"
RDL4-ADJ-30K		10W	3000K	650LM	
RDL4-ADJ-41K		10W	4100K	650LM	
RDL4-ADJ-50K		10W	5000K	650LM	
RDL6-ADJ-27K		12W	2700K	900LM	5"/6"
RDL6-ADJ-30K		13W	3000K	900LM	
RDL6-ADJ-41K		13W	4100K	900LM	
RDL6-ADJ-50K		13W	5000K	900LM	



RDL-ADJ



TECHNICAL SPECIFICATIONS:

- :: Die-cast aluminum with white powder coat finish
- :: Trim ring: Integrated spun aluminum white powder coat finish
- :: Gasket: close cell Neoprene foam gasket
- :: Lens: 0.125" white translucent acrylic
- :: Isolated driver for improved thermal management
- :: CRI: 90
- :: Working Voltage: 120V AC
- :: Dimmable
- :: Tilts to 45°
- :: Can rotate after installation to align
- :: LED: EPISTAR chip (COB) and driver—35,000-hour design life
- :: Power factor: 90% +
- :: Suitable for damp locations
- :: Maximum Ambient Temperature: 104°F
- :: UL-listed
- :: Energy Star-rated



ACCESSORIES INCLUDED







Includes medium base
E-26 screw-in adaptor
that fits any standard
incandescent downlight



GU24 Adaptor that
fits any GU24 socket

LED DOWNLIGHTS (ADJUSTABLE)—4" & 5"/6" ROUND

CATALOG NO.		WATTS	COLOR TEMP	LUMENS	DIAMETER
RDL4-ADJ-27K		10W	2700K	650LM	4"
RDL4-ADJ-30K		10W	3000K	650LM	
RDL4-ADJ-41K		10W	4100K	650LM	
RDL4-ADJ-50K		10W	5000K	650LM	
RDL6-ADJ-27K		12W	2700K	900LM	5"/6"
RDL6-ADJ-30K		13W	3000K	900LM	
RDL6-ADJ-41K		13W	4100K	900LM	
RDL6-ADJ-50K		13W	5000K	900LM	

