

Eaton REN-15

Catalog Number: REN-15

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 15 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Photo is representative

| | |
|--------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton Bussmann series REN fuse | REN-15 |
| UPC | Product Length/Depth |
| 051712100151 | 2 in |
| Product Height | Product Width |
| 0.56 in | 0.56 in |
| Product Weight | Warranty |
| 0.55 lb | Not Applicable |
| Compliances | |
| Not Applicable | |

Electrical rating

Amperage Rating

15 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[REN-15~SUPER LAG RENEW. FUSE 15/250](#)

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-15](#)