

# Eaton REN-30

Catalog Number: REN-30

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series REN fuse	REN-30
<b>UPC</b>	<b>Product Length/Depth</b>
051712100304	2 in
<b>Product Height</b>	<b>Product Width</b>
0.56 in	0.56 in
<b>Product Weight</b>	<b>Warranty</b>
0.55 lb	Not Applicable
<b>Compliances</b>	
Not Applicable	

## Electrical rating

### Amperage Rating

30 A

### Interrupt rating

10 kAIC

### Voltage rating

250 V

## Physical details

### Packaging type

Standard

## General information

### Class

Class H

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Quantity

10

### Special features

Super lag, time lag, non current-limiting

## Resources

### Catalogs

[REN-30-SUPER LAG RENEWABLE FUSE 30/250](#)

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - REN-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)