



Mark 10 Powerline

MARK 10 POWERLINE ELE DIMMING BALLAST (2) F54T5/HO 120V

For companies looking to make their fixed-output linear T8, 4-pin CFL, and T5/HO fluorescent systems more cost effective and sustainable, Mark 10 Powerline ballasts provide an easy solution without the need for additional control leads. Simply, (1) replace the ballast, (2) replace the switch, (3) dim the lights, that is all it takes. It's that easy to bring the convenience and flexibility of fluorescent dimming to conference rooms, private offices, auditoriums, architectural cove lighting — anywhere dimming is required.

Product data

General Information			
Lamp Type	F54T5/HO		
Number of Lamps	2 piece/unit		
Ballast Type	Dimmable Fluorescent		
Base Model	REZ2S54		
Suitable For Outdoor Use	Yes		
Automatic Restart	Yes		
Operating and Electrical			
Input Voltage	120 V		
Input Frequency	60 Hz		
Total Harmonic Distortion USA	10 %		
Ignition Method	Programmed Start		
Crestfactor (Nom)	1.7		
Ignition Time (Nom)	1.5 s		
Ballast Factor (Max)	1		
Ballast Factor (Min)	0.03		
Power Factor (Nom)	0.98		
Input Current (Nom)	1.05 A		

Input Power (Max)	125 W
Input Power (Min)	24 W
Rated Lamp Power	54 W
Wiring	
Color Input Terminals	Black and White
Color Output Terminals	RED, YEL & BLU
Wire Striplength	0.375 mm
Control Wire Gauge	NA
Lamp Connection	Series
Wire Length by Color	No wires
Wire Gauge (Nom)	18AWG mm
Wire Type	Solid
Remote Wiring Configuration Allowed	No
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	Yes
Max Ballast-Lamp Distance Remote Wiring	No Remote
Max Ballast-Lamp Distance Tandem Wiring	No Tandem
Max Ballast-Lamp Distance Through Wiring	Blue = 5'


Datasheet, 2019, March 22 data subject to change

Mark 10 Powerline

Connector Type	Poke-In
Temperature	
T-Case Maximum (Nom)	70 °C
Mechanical and Housing	
Housing Material	Metal
Housing	D
Housing Dimensions	16.7" × 1.18" × 1.0"
Approval and Application	
EMC Immunity Standard	FCC Consumer
Approval Marks	CSA certificate UL certificate CEC Listing
	NOM certificate RoHS Compliant

Hum And Noise Level	А			
UL Recognized	No			
Product Data				
Order product name	MARK 10 POWERLINE ELE DIMMING			
	BALLAST (2) F54T5/HO 120V			
EAN/UPC - Product	781087107348			
Order code	913700500541			
Numerator - Quantity Per Pack	1			
Numerator - Packs per outer box	12			
Material Nr. (12NC)	913700500541			
Net Weight (Piece)	0.432 kg			

Dimensional drawing



ELE DIMMING BALLAST (2) F54T5/H0 120V

Product	A1	A2	B1	C1
MARK 10 POWERLINE ELE DIMMING	16.70 in	16.34 in	1.18 in	1.00 in
BALLAST (2) F54T5/HO 120V				



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.