Eaton RF9601DW

Catalog Number: RF9601DW

Eaton Z-Wave plus decorator switch, Power Failure Memory, 15A, 120V, White, 60 Hz, LED, CFL, incandescent, MLV, ELV, fluorescent, and halogen, Single-pole, Three-way, Multi-location, Used with RF9517



Product Name Eaton Z-Wave Plus decorator switch Catalog Number **RF9601DW**

032664755187

Product Height 3.81 in

UPC

Product Weight 0.001 lb

Compliances FCC Compliant Product Length/Depth

Product Width 1.8 in

Warranty

1.38 in

2 year limited

Certifications

cULus Listed NOM





Product specifications

Special features

Power Failure Memory

Switch type

Single-pole, multi-location

Load type

FLR LED CFL HAL ELV INC

MLV

Color

White

Wiring method

Wire leads

Amperage Rating

15A

Number Of Poles

Single-pole

Туре

Decorator switch

Frequency rating

60 Hz

Operating temperature

32 to 104 °F (0 to 40 °C)

Number of ways

Three-way

Voltage rating

120 V

Torque rating

12-14 lbf-inch

Resources

Installation instructions Z-Wave Plus wireless switch spec sheet Z-Wave Plus wireless switch and accessory switch (RF9601, RF9617) instruction sheet Multimedia Eaton's new Z-Wave Plus wireless collection Specifications and datasheets

Eaton Specification Sheet - RF9601DW



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia