

Eaton RF9643-NDW

Catalog Number: RF9643-NDW

Eaton Z-Wave plus dimmer switch, White, Single pole, 120 Vac, 300W Dimmable LED/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Dimmer switch, Multi-location, 32°F to 104°F (0°C to 40°C)



General specifications

Product Name	Catalog Number
Eaton Z-Wave plus dimmer switch	RF9643-NDW
UPC	Product Length/Depth
032664757402	1.42 in
Product Height	Product Width
4.2 in	1.8 in
Product Weight	Certifications
0.01 lb	NOM cULus Listed

Product specifications

Switch type

Dimmer switch

Phase

Single-phase

Termination style

Back and side wire

Load type

300 W for LED, CFL

600 W for INC, HAL, FLR, MLV, ELV

Color

White

Wiring method

Back and side

Material

Polycarbonate

Mounting method

Flush

Number Of Poles

Single-pole, Three-way

Number of gangs

2

3

1

Style type

Decorator

Environmental conditions

Dry

Frequency rating

60 Hz

Connection type

Back

Side

Operating temperature

32 to 104 °F (0 to 40 °C)

Number of ways

Resources

Multimedia

[Eaton's new Z-Wave Plus wireless collection](#)

Specifications and datasheets

[Eaton Specification Sheet - RF9643-NDW](#)

Three-way

Voltage rating

120 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)