

Specifications



Eaton RI06P-W

Eaton rotary dimmer, Power failure memory, with preset, #16 AWG, 5A, 120V, Wire lead, Maintained closure, White, Indoor, 60 Hz, Incandescent, halogen, 0° to 40°C, Single-pole, three-way, Polycarbonate, 600W

General specifications

PRODUCT NAME	Eaton rotary dimmer
CATALOG NUMBER	RI06P-W
UPC	032664699023
PRODUCT LENGTH/DEPTH	2.3 in
PRODUCT HEIGHT	4.75 in
PRODUCT WIDTH	3.06 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	NOM cULus Listed
PRODUCT TYPE	Rotary dimmer



Powering Business Worldwide

Product specifications

FREQUENCY RATING	60 Hz
SPECIAL FEATURES	Power failure memory, with preset
AMPERAGE RATING	5 A
VOLTAGE RATING	120 V
ALLOWABLE WIRE SIZE	#16 AWG
OPERATING TEMPERATURE	0 to 40 °C
WIRING METHOD	Wire lead
WATTAGE	600 W
ENVIRONMENTAL CONDITIONS	Indoor
SWITCH TYPE	Single-pole, three-way
MOUNTING METHOD	Flush
CLOSURE TYPE	Maintained
LOAD TYPE	INC HAL
MATERIAL	Polycarbonate
COLOR	White

Resources

INSTALLATION VIDEOS	How to install Eaton's universal slide dimmers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - RI06P-W Rotary dimmers and fan controls spec sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

