



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RL124H Lampsocket, 600W 600V, Med W/Hook, NM *Hubbell Wiring Devices*

Catalog Number	RL124H
Manufacturer	Hubbell Wiring Devices
Description	Hubbell Wiring Device Kellems, Lamp Holders and Sockets, Medium Base, 660W 600V Ac, Non-Metallic, With Hook
Weight per unit	0.0500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	2.64
connection	Insulation Piercing
Current Rating	2.64
Item Type	Replacement Incandescent Lampholders
lamp size	Medium Base
Material	COMPOSITE
Voltage Rating	250V AC kV

Material, Color, and Finish

Color	Black
-------	-------

Descriptions

Description	LAMPSOCKET, 600W 600V, MED W/HOOK, NM
extra long description	HWDK RL124H LAMPSOCKET, 600W 600V,
Long Description	Hubbell Wiring Device Kellems, Lamp Holders and Sockets, Medium Base, 660W 600V AC, Non-Metallic, with Hook
Product Type	Lampsocket, 600W 600V, Med W/Hook, NM
Special Features	Pull Chain

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778112249
Manufacturers Part Number	RL124H
series	Lampholder Accessories
sub brand	Lighting Control
UPC	883778112249

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous commercial & industrial devices
Type	Incandescent, Medium Base

Packaging

Carton	10
Package	1
Weight Per each	0.05



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Medium Base Light Stringer Style
Frequency Rating	60
Mounting	Socket with Hook
standard	C/US UL Listed