

Standard

STANDARD MAG BALLAST (1) F40T12 RS 120V

Available for many fluorescent lamp types sold today, including Preheat, Rapid Start, 2-pin CFL, Slimline, High Output, Very High Output and Circline. Magnetic ballasts can be used in any application where these lamps are used.

Product data

General Characteristics

Lamp Type Number of Lamps Input Voltage Input Current (Oper- ating)	F40T12 1 piece 120 V 0.53 A
Line Frequency	60 Hz
Lamp Footage(for	-
sign ballast)	
Ballast Type	Magnetic Fluorescent
Base Model	RL140TP
Housing	R4
Housing Dimensions	6.5" x 1.94" x 1.38"
Housing Material	Metal
Suitable for Outdoor	Yes
use?	
Starting Method	Rapid Start
Family Name	Standard

• Operating Characteristics

Automatic restart	Yes	
Ignition time	1 s	
Input Power Gear	32 W	
Ballast factor	0.63 -	
Ballast Efficacy Factor	2.01 -	
Power Factor	0.55	
Lamp Current Crest	1.5 -	
Factor		
Sound Rating	А	
Max THD	15 %	

• Wiring Characteristics

Wire Striplength	0.50/0.375 mm
Lamp Connection	Series
Wire Gauge	18AWG

Wire Length by	See data sheet
Color	C 11 1
Wire Type	Solid
Allowed Wiring	Yes
Config(Remote)	
Allowed Wiring	No
Config(Tandem)	
Allowed Wiring	No
Config(Through)	
Max Dist. Ball to	30'
Lamp(Remote)	
Max Dist. Ball to	-
Lamp(Tandem)	
Max Dist.Ball to	-
Lamp(Through)	

• System Chars on driver level

Rated Lamp Watts 40W

• Product Dimensions

Length A1	6.5 in		
Length A2	6 in		
Width B1	1.94 in		
Height C1	1.38 in		

• Approval & Application Chars

EMC Immunity	FCC Non-Consumer
Approbation Marks	UL, CSA, RoHS
UL Listed	Yes
CSA certificate	Yes
CEC Listing	No
Circle E logo	No
CSA E	No
cUL certificate	No




Standard

DOE	No
FIDE Certificate	No
NOM certificate	No
RoHS Compliant	Yes
SASO Certificate	No
UL Recognized	No


• Product Data

Product number

Dimensional drawing



RL140TPI



Full product name Short product name Pieces per Sku eop_pck_cfg Skus/Case Bar code on pack Bar code on case Logistics code(s) eop_net_weight_pp

MAG BALLAST (1) F40T12 RS 120V MAG BALLAST (1) F40T12 RS 120V 1 10 781087105320 30781087105321 913700501061 0.903 kg

STANDARD MAG BALLAST (1) F40T12 RS 120V

Product	A1 (Norm)	A2 (Norm)	B1 (Norm)	C1 (Norm)	D1 (Norm)
MAG BALLAST (1) F40T12 RS 120V	6.5	6	1.94	1.38	-



© 2014 Koninklijke Philips N.V. (Royal Philips) All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting