



The HALO® RL LED Recessed Trim series includes 3", 4", and 5"/6" LED baffle-trim module for recessed downlights. This series provides ultimate personalization with 5 Selectable CCT, a Dim-to-Warm setting, and selectable lumens. During installation select the perfect color temperature for your space with 5 color temperatures between warm (2700K) to daylight (5000K) or a dim-to-warm setting. The dim-to-warm setting begins at 3000K and dims smoothly to 1800K, creating a rich, warm glow resembling candlelight or the sun on the horizon. Depending on your ceiling height or desired light level choose one of the selectable lumen enabled fixtures.

It is designed for use in new construction, remodel and retrofit installation in HALO and other compatible 3", 4", 5"/6" recessed downlight housings.

## Product Features

- Baffle Trim with regressed lens
- Available in 3", 4", 5"/6" aperture
- Compatible with most recessed housings
- 5-color selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K, plus D2W
  - Dim-to-warm technology included: use your dimmer to warm color temperature from 3000K to 1800K
- Selectable Lumen: RL4LS: 600/900 Lumens; RL56LS: 900/1200 Lumens
- 120V input, dimmable down to 5% with select phase cut dimmers
- Air-tite, wet location listed, IC rated



LEARN MORE



3"

RL3059FSD2W1EWH



4"

RL4LS9FSD2W1EWH



5"

6"

RL56069FSD2W1EWH  
RL56LS9FSD2W1EWH

## Personalize Your Lighting



Select the perfect color temperature for your space with 5 color temperatures between warm (2700K) to daylight (5000K) or a dim-to-warm setting.



Choose between 2 lumen options (900-1200) depending on your ceiling height or desired light level.



dim-to-warm  
set the mood

3000K 1800K

The dim-to-warm setting begins at 3000K and dims smoothly to 1800K, creating a rich, warm glow resembling candlelight or the sun on the horizon.

Catalog Number	Material Number	Description	UPC	Accessories
				Designer Trims
RL3059FSD2W1EWH	13601497	3" LED Recessed Trim, 500 lumens, 90 CRI, 120V 60Hz, LE & TE phase cut 5% dimming, Selectable D2W, 2700, 3000, 3500, 4000, or 5000K CCT	080083257669	<b>RL3TRMMW</b> Matte White <b>RL3TRMMB</b> Matte Black <b>RL3TRMSN</b> Satin Nickel <b>RL3TRMTBZ</b> Tuscan Bronze
RL4LS9FSD2W1EWH	13601498	4" LED Recessed Trim, 600/900 Selectable lumens, 90 CRI, 120V 60Hz, LE & TE phase cut 5% dimming, Selectable D2W, 2700, 3000, 3500, 4000, or 5000K CCT	080083257683	<b>RL4TRMWHB</b> Matte White, Baffle <b>RL4TRMWBB</b> Matte Black, Baffle <b>RL4TRMSNB</b> Satin Nickel, Baffle <b>RL4TRMTBZB</b> Tuscan Bronze, Baffle <b>RL4TRMWH</b> Matte White, Splay <b>RL4TRMMB</b> Matte Black, Splay <b>RL4TRMSN</b> Satin Nickel, Splay <b>RL4TRMTBZ</b> Tuscan Bronze, Splay
RL56069FSD2W1EWH	13601550	5"/6" LED Recessed Trim, 600 lumens, 90 CRI, 120V 60Hz, LE & TE phase cut 5% dimming, Selectable D2W, 2700, 3000, 3500, 4000, or 5000K CCT	080083258925	<b>RL56TRMWHB</b> Matte White, Baffle <b>RL56TRMMBB</b> Matte Black, Baffle <b>RL56TRMSNB</b> Satin Nickel, Baffle <b>RL56TRMTBZB</b> Tuscan Bronze, Baffle <b>RL56TRMWH</b> Matte White, Splay <b>RL56TRMMB</b> Matte Black, Splay <b>RL56TRMSN</b> Satin Nickel, Splay <b>RL56TRMTBZ</b> Tuscan Bronze, Splay
RL56LS9FSD2W1EWH	13601551	5"/6" LED Recessed Trim, 900/1200 Selectable lumens, 90 CRI, 120V 60Hz, LE & TE phase cut 5% dimming, Selectable D2W, 2700, 3000, 3500, 4000, or 5000K CCT	080083258949	