



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RMJS8TDVB Powpak 0-10V 434

Lutron

Catalog Number	RMJS8TDVB
Manufacturer	Lutron
Description	Powpak Dimming Module, Controls Up to 60 Ma Of 0-10V Controlled Fixtures Together, Switches Up to 8 A, 120/277 Vac, 434 MHZ, Vive Enabled
Weight per unit	0.3100 (lbs/each)
Product Category	Lighting Dimmers

Features

load	0 to 10
Material	Plastic
Poles	1
Voltage Rating	120 to 277

Material, Color, and Finish

Color	Green/White
-------	-------------

Dimensions and Weight

Size	3.94 x 2.82
------	-------------

Descriptions

Description	POWPAK 0-10V 434
extra long description	LUT RMJS-8T-DV-B POWPAK 0-10V 434
Long Description	PowPak dimming module, controls up to 60 mA of 0-10V controlled fixtures together, switches up to 8 A, 120/277 VAC, 434 MHz, Vive enabled
Product Type	Powpak 0-10V 434
Special Features	Controls LED/fluorescent fixture loads. 0-10V analog control is widely used in the fixture industry. Automatically adjusts to both sink and source LED and fluorescent fixtures.

Manufacturer Information

Brand	Lutron
GTIN	00784276159722
Manufacturers Part Number	RMJS-8T-DV-B
UPC	784276159722

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimming module for 0-10V control

Packaging

Carton	1
Weight Per each	0.31



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	0 to 90% humidity, non-condensing. Indoor use only.
Frequency Rating	431 to 437
Mounting	JUNCTION BOX
Operating Temperature	32 to 104
standard	UL, cUL, FCC, ICC, COFETEL, NOM