

Specifications

Eaton RSPF2403SA2A

Eaton Surge Protection Device for sub-panel, RSPF Series, F Frame, 120/208Y, 127/220Y, 240D rating, integrated, Basic feature package plus filtering, Direct Bus Mounted

General specifications

PRODUCT NAME	Eaton RSPF surge protection device
CATALOG NUMBER	RSPF2403SA2A
UPC	786689030605
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	7.5 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	2.38 lb
WARRANTY	2 year
CERTIFICATIONS	UL 1449 UL Listed

Product specifications

ACCESSORIES	Basic Plus Filtering
--------------------	----------------------

FREQUENCY RATING	50/60 Hz
-------------------------	----------

NOMINAL DISCHARGE CURRENT	20 kA
----------------------------------	-------

USED WITH	Direct bus mounted
------------------	--------------------

PHASE	Three-phase
--------------	-------------

OPERATING TEMPERATURE	-40 to 60 °C
------------------------------	--------------

TYPE	SPD
-------------	-----

SPECIAL FEATURES	Meets or exceeds the requirements specified in IBC ®2006, CBC2007, and UBC®Zone 4
-------------------------	---

Resources

CATALOGS

[Power Distribution and Control Assemblies, SPD, Power Conditioning, PF Capacitors and Harmonic Filters, Volume 3, Tab 2](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - RSPF2403SA2A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Eaton RSPF2403SA2A

Eaton Surge Protection Device for sub-panel, RSPF Series, F Frame, 120/208Y, 127/220Y, 240D rating, integrated, Basic feature package plus filtering, Direct Bus Mounted

General specifications

PRODUCT NAME	Eaton RSPF surge protection device
CATALOG NUMBER	RSPF2403SA2A
UPC	786689030605
PRODUCT LENGTH/DEPTH	5 in
PRODUCT HEIGHT	7.5 in
PRODUCT WIDTH	5 in
PRODUCT WEIGHT	2.38 lb
WARRANTY	2 year
CERTIFICATIONS	UL 1449 UL Listed

Product specifications

ACCESSORIES	Basic Plus Filtering
--------------------	----------------------

FREQUENCY RATING	50/60 Hz
-------------------------	----------

NOMINAL DISCHARGE CURRENT	20 kA
----------------------------------	-------

USED WITH	Direct bus mounted
------------------	--------------------

PHASE	Three-phase
--------------	-------------

OPERATING TEMPERATURE	-40 to 60 °C
------------------------------	--------------

TYPE	SPD
-------------	-----

SPECIAL FEATURES	Meets or exceeds the requirements specified in IBC ®2006, CBC2007, and UBC®Zone 4
-------------------------	---

Resources

CATALOGS

[Power Distribution and Control Assemblies, SPD, Power Conditioning, PF Capacitors and Harmonic Filters, Volume 3, Tab 2](#)

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - RSPF2403SA2A](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

