

Clamps >

Right Angle Clamps



Stainless



Description

Robroy Stainless Right Angle Clamps are made from 316 stainless steel and are designed to secure rigid or PVC-coated conduit perpendicular to beam, channel and angle supports.

Standards

- cULus Listed
- UL 2239
- UL File Number: E216996

Catalog No.	Description	Weight Each (lbs.)
RSRAC116	Right Angle Clamp 1/2 Inch 316	0.30
RSRAC216	Right Angle Clamp 3/4 Inch 316	0.34
RSRAC316	Right Angle Clamp 1 Inch 316	0.39
RSRAC416	Right Angle Clamp 1-1/4 Inch 316	0.44
RSRAC516	Right Angle Clamp 1-1/2 Inch 316	0.52
RSRAC616	Right Angle Clamp 2 Inch 316	0.71
RSRAC716	Right Angle Clamp 2-1/2 Inch 316	0.90
RSRAC816	Right Angle Clamp 3 Inch 316	1.04
RSRAC1016	Right Angle Clamp 4 Inch 316	1.27