



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

132 Professional Dr.
72023-0000, AR Cabot
Phone: 501-605-1780
Fax: 501-605-1785

RX142WGPCS 14/2 WG Romex-Pieces *Southwire Company*



Catalog Number	RX142WGPCS
Manufacturer	Southwire Company
Description	Non-Metallic Sheathed Cable, Color-Coded Cable Jacket Additional Information, Dry Location;Residential Application, Copper Conductor Material, 14 Awg Conductor Size, 15 A Current Rating, Polyvinyl Chloride (PVC) Insulation Material, 19 Mil Insulation Thickness, Nylon Jacket Material, Made In Usa, +90 °C Maximum Operating Temperature, 2 - Conductors, 1 - Strands, 368 Mil Overall Length, Carton Package Type, Strand Solid/Strand, Astm B-3 and B-8;Federal Specification A-A-59544;Nfpa 70;Reach/Rohs Compliant;UI
Weight per unit	0.0580 (lbs/ft)
Product Category	NM-B - NMD90

Descriptions

Also Known As...	Non-Metallic Sheathed Cable 220 Wire Thermoplastic-Sheathed Cable
Description	14/2 WG ROMEX-PIECES
similar brands	Romex®

Manufacturer Information

Brand	Copper
-------	--------

Taxonomies, Classifications, and Categories

Category Description	ROMEX (RX)& UF CABLE
----------------------	----------------------

Packaging

Carton	1
Weight Per foot	0.058