Eaton S10N04A82N

Catalog Number: S10N04A82N

Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 54, 60 Hz, single-phase, 120 V, 240 V, 12/24 V, NONE, 115 °C rise, 0.1 KVA, indoor-outdoor, 3B

General specifications

Product Name Eaton General purpose encapsulated	Catalog Number S10N04A82N	
transformer	UPC 786680383106	
Product Length/Depth	Product Height	
4 in	8.5 in	
Product Width 4.11 in	Product Weight 7 Ib	
Warranty	Certifications	
Eaton Selling Policy 25-000, one (1) year UL Listed		
from the date of installation of the	Catalog Notes	
Product or eighteen (18) months from the	Model N	
date of shipment of the Product,		
whichever occurs first.		



Photo is representative



Physical Attributes

0.1	Concernent of the Land
(:01	material
000	matoma

Aluminum

Design

EΡ

Enclosure

NEMA 3R

Frame

54

Tap size

None

Туре

Buck-Boost General-Purpose Encapsulated Transformer

Wiring connection

3B

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage 12/24 V

Temperature rise

115 °C rise

Volt ampere rating

0.1 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S10N04A82N



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia