



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S10N04P51P .5KVA Buck Boost Transformer 1PH 120X240-12/24V

Eaton Corp

Catalog Number	S10N04P51P
Manufacturer	Eaton Corp
Description	Dry Type Transformer, 120 X 240 V, 12/24 V, 0.50 K Va Va Rating, Encapsulated Transformer, 5.18 In Overall Length, 4.45 In Overall Width, 9.34 In Overall Height, 60 HZ, 115 °C Temperature Rise Rating, 15 LB
Weight per unit	17.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

Features

connection	509A
design	EP
dimensions	5.1800 IN X 4.4500 IN X 9.3400 IN
frame	57P
Number of Phases	Single-phase
Secondary Voltage	12/24 V

Descriptions

Description	.5KVA BUCK BOOST TRANSFORMER 1PH 120X240-12/24V
extra long description	ETN S10N04P51P .5KVA BUCK BOOST XFM

Manufacturer Information

GTIN	00786680073588
UPC	786680073588

Taxonomies, Classifications, and Categories

Category Description	BUCK & BOOST TRANSFORMERS
Type	Encapsulated transformer

Packaging

Carton	1
Weight Per each	17

Uses, Certifications, and Standards

Frequency Rating	60 Hz
standard	UL Listed
Temperature Rating	115 °C rise