

Project Name

Location

Prepared By



SATCO S11258

15PAR38/LED/RGB/TW/SF

Notes

[www] 11-22-2021 02:57:41

General

Status	Active
Watts	15W
Incandescent Equivalent	90W
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700K-5000K
Temperature	Warm to Cool White/Color Changeable
CRI	80
Lumens	1200L
Beam Spread	40
Dimmable	Yes-Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Smart Product Info

IOT Enabled	Yes
Operational Humidity	10% - 80% R.H.
Number of Switching Cycles	7500
Software Upgradeable	Yes
Start Up	100% coldlight
Communication Protocol	WiFi
Voice Assistants Supported	Siri; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

Electrical

Operating Frequency	60 Hz
---------------------	-------

Specifications

Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	5.00
MOD	4.72
Housing Color	White
Lens Finish	Plastic (PS)
Lens Material	Plastic (PS)
Weight (lb.)	0.33

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 3 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes

ES Unique ID	ESID-2368909
California Status	Non-Compliant
California Compliant Substitute	S11277
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Copyright 2020 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
<http://www.satco.com/>

