



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street
72701-0000, AR Fayetteville
Phone: 479-443-4948
Fax: 479-443-6465



S11277 *Discontinued* 15W Led PAR38 RGB/27K-5K Starfish Satco

Catalog Number	S11277
Manufacturer	Satco
Description	15 Watt - PAR38 Led - RGB & Tunable White - Starfish lot - 120 Volt - 1200 Lumens - T20 - 90 Cri
Weight per unit	0.5200 (lbs/each)
Product Category	Lighting

Features

average life	25000
Base	E26
beam angle	40
dimnable	Yes-Dimmable
lumens	1200
Power Factor	0.9
Voltage Rating	120
Wattage	15

Material, Color, and Finish

color rendering index (cri)	90+
color temperature	2700 to 5000

Descriptions

Description	*DISCONTINUED* 15W LED PAR38 RGB/27K-5K STARFISH
extra long description	SATCO S11277 15PAR38/LED/RGB/TW/T20
Long Description	15 Watt - PAR38 LED - RGB & Tunable White - Starfish IOT - 120 Volt - 1200 Lumens - T20 - 90 CRI
Product Type	15PAR38/Led/RGB/TW/T20/SF
Special Features	Warranty: 5-Years ; Location Rating: Wet ; Operating Temp: -20C (-4F) to +45C (+113F) ; Dimmable Text: Only with Starfish App ; Material: Plastic ; Indoor Outdoor: Indoor;Outdoor ; Color Temp: Warm to Cool White/Color Changeable ; Efficacy: 80.00 LPW ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor;Outdoor ; Lamp Filament: LED ; ANSI Base: E26 ; Amps: 0.125A ; T24 Compliant: True

Manufacturer Information

Brand	Satco
GTIN	00045923112775
Manufacturers Part Number	S11277
UPC	045923112775



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

555 E. 15th Street
72701-0000, AR Fayetteville
Phone: 479-443-4948
Fax: 479-443-6465

Taxonomies, Classifications, and Categories

Category Description LED PAR SHAPE LAMPS

Type LED Directional

Availability

Status Inactive

Packaging

Carton 1

Package 6

Weight Per each 0.52

Uses, Certifications, and Standards

Application LED

standard cULus - Certified;cULus - Listed