



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S11417 9.5W A19 Led 50K E26 120V Dimmable 4-PK

Satco

Catalog Number	S11417
Manufacturer	Satco
Description	9.5 Watt A19 Led - 5000K - Dimmable - Medium Base - 230 Degree Beam Angle - 4-Pack
Weight per unit	0.4200 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E26
beam angle	230
dimmable	Yes-Dimmable
lumens	800
Material	Polycarbonate (PC); High Heat Conductive Plastic Housing
Power Factor	0.76
Shape	A19
Voltage Rating	120
Warranty	3 Year Limited
Wattage	9.5

Material, Color, and Finish

color rendering index (cri)	80+
color temperature	5000
Finish	white

Descriptions

Description	9.5W A19 LED 50K E26 120V DIMMABLE 4-PK
extra long description	SATCO S11417 9.5A19/LED/850/120V/D/
Long Description	9.5 Watt A19 LED - 5000K - Dimmable - Medium Base - 230 Degree Beam Angle - 4-Pack
Product Type	9.5A19/Led/850/120V/D/4PK
Special Features	Warranty: 2-Years ; Location Rating: Damp ; Operating Temp: -20C (-4F) to +45C (+113F) ; Material: Polycarbonate (PC) / High Heat Conductive Plastic Housing ; Indoor Outdoor: Indoor ; Color Temp: Natural Light ; Efficacy: 84.21 LPW ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor ; Lamp Filament: LED ; ANSI Base: E26 ; Amps: 0.079A ; T24 Compliant: False



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923114175
Manufacturers Part Number	S11417
UPC	045923114175

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	LED General Service

Packaging

Carton	1
Weight	0.08
Weight Per each	0.42

Uses, Certifications, and Standards

Application	LED
Operating Temperature standard	-20C (-4F) to a maximum of +45C (+113F) cULus - Certified;cULus - Listed