



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **S11851 6" 15W Led Commercial DNLT 27K/3K/35K/4K/5K 1600L**

*Satco*

Catalog Number	S11851
Manufacturer	Satco
Description	15-Watt Commercial Led Downlight - 6 In. - CCT Adjustable - 120-277 Volts - Econo
Weight per unit	1.1 (lbs/each)
Product Category	Lighting

### **Features**

amperage rating	0.14
average life	50000
Base	Integrated LED
beam angle	90
Lamp Included	Integrated
Lamp Type	LED
Material	Aluminum
Socket Type	Integrated
Voltage Rating	120 to 277 v
Wattage	15

### **Material, Color, and Finish**

Color	White
Finish	white
Style	Utility

### **Dimensions and Weight**

Height	3.46
Length	7.4
Size	H:3.00 D:7.40
Width	7.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	6" 15W LED COMMERCIAL DNLT 27K/3K/35K/4K/5K 1600L
extra long description	SATCO S11851 15WLED/CDL/6/CCT/120-2
Long Description	15-Watt Commercial LED Downlight - 6 in. - CCT Adjustable - 120-277 Volts - Econo
Product Type	15WLED/CDL/6/CCT/120-277
Special Features	Amps: 0.140A; Beam Angle (degree): 90; Bulb Included: Integrated; Can Size: 6 in.; Cct Selectable: True; Ceiling Aperture: 6.02; Color Temp: Warm to Cool White; Fluor Equiv: 1 x 26W CFL; Incandescent Equivalent: 75W; Indoor Outdoor: Indoor; JA8 Compliant: False; Lens Material: Polycarbonate (PC); Location Rating: Wet; Mounting Procedure: Ceiling; NSF Approved: No; Operating Frequency: 50/60Hz; Operating Temp: -20C (-4F) to +40C (+104F); Outdoor; Power Factor: 0.99; Replaceable Light Source: False; Style: Utility; Warranty: 5-Y

## Manufacturer Information

Brand	Satco
GTIN	00045923118517
Manufacturers Part Number	S11851
UPC	045923118517

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED LIGHTING

## Trade Size

aperture size	6.02.
---------------	-------

## Packaging

Carton	1
Package	8
Weight Per each	1.05

## Uses, Certifications, and Standards

Application	Recessed
Frequency Rating	50/60 Hz
Mounting	CEILING
standard	cETLus - Listed